

The Aquabatch

Hair and Lint Removal in tunnel washers

hair and lint free!



- ◆ Removes hair and lint in the rinse zone of tunnel washers
- ◆ Supports water saving actions
- ◆ Premium hygiene solution due to closed system
- ◆ Best results due to back flushing with fresh water
- ◆ Low maintenance

Tested by **Institute Hohenstein**

ECOLAB[®]

Everywhere It Matters.[™]

Do you have lint and hair complaints from your customers?

Due to the state of the art water consumption on tunnel washer, lint and hair on textiles have become a serious issue in professional laundries. Additionally, a lower cotton quality leads to more lint in the rinse zone.

THE SOLUTION

The Aquabatch is a filter system which is specially designed to remove hair and lint out of a tunnel washer. Water is pumped out of the rinse zone, filtered and re-transferred into the same compartment.

BENEFITS

- ◆ Excellent reduction of lint and hair on textiles
- ◆ Improved customer satisfaction
- ◆ Premium hygiene solution due to closed system
- ◆ Low maintenance



FUNCTIONALITY

- ◆ Water is pumped out of the rinsing zone at the lowest point
- ◆ Filtered water is re-transferred into the same compartment of tunnel washers
- ◆ The system works automatically - automatic back flush included
- ◆ Water circulation capacity variable up to 15 m³/hour
- ◆ Total volume of water is filtered up to 3 times within one batch cycle
- ◆ Flexible filter size (115 µm / 130 µm / 200 µm)